



SPRAY CABINET DEGREASER



SPRAY CABINET DEGREASER is a non-foaming blend of alkalinity builders, sequestrants and defoamers designed to be used in recirculating spray cabinet cleaners. It has a special buffered alkalinity that minimizes attack on aluminum and other alloys, but it has plenty of reserve strength to dissolve baked-on oil and varnish residues from transmissions and other aluminum parts. It saves labor by cleaning quickly without using large amounts of chemical. Spent solutions of spray cabinet degreasers releases oil easily making them easy to dispose of. This special designed formula does not contain phosphates and has an extremely low cod level.

SPECIFICATIONS:

Physical Appearance.....	Yellow powder
Odor.....	No odor
Specific Gravity.....	N/A
pH.....	12.0 (use dilution)
viscosity.....	N/A
Biodegradable	Yes
Freeze point.....	N/A
Phosphorous as % P.....	None
Flash point.....	None

DIRECTIONS:

Use **SPRAY CABINET DEGREASER** at 4 to 8 ounces per gallon of water. Maintain the vat solution at 140 to 180 degree for maximum effectiveness.

WARNING:

May be irritating to skin and eyes. Contains sodium metasilicate and sodium carbonate. Keep container closed. Product absorbs moisture from the air. Do not transfer to unmarked container. Use with adequate ventilation.

FIRST AID:

If eye contact occurs, immediately flush with water for 15 minutes. Get medical attention immediately. For **skin**, wash with water for 15 minutes. Get medical attention immediately. For **ingestion**, do not induce vomiting. Never give anything by mouth to an unconscious person. Get medical attention immediately. If **inhaled**, remove individual to fresh air. If breathing is difficult, administer oxygen. If breathing has stopped give artificial respiration. Keep person warm, quiet and get medical attention.

ETOWAH CHEMICAL SALES & SERVICE

PO BOX 4416 ***** Gadsden, Alabama 35904

1-800-848-8541